

H0,75/14D GR BD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Version	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
Order No.	9004300000
Type	H0,75/14D GR BD
GTIN (EAN)	4008190154837
Qty.	500 pc(s).
Packaging	Reel packaged

H0,75/14D GR BD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.086 g
------------	---------

Technical data

Description of article	Linked wire-end ferrules, grey	Version	Standard
------------------------	--------------------------------	---------	----------

Wire-end ferrules

Collar diameter (D2)	2.8 mm	Colour code	DIN
Conductor cross-section	0.75 mm ²	Contact surface diameter (D1)	1.2 mm
Contact surface length (L2)	8 mm	L1 in mm	14 mm
Metal sleeve thickness (S1)	0.15 mm	Military designation	T 20A 005 A
Plastic collar thickness (S2)	0.25 mm	Stripping length	10 mm
Wire connection cross section AWG, max.	AWG 18		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

H0,75/14D GR BD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

