

H4,0/19,5X GR SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Polypropylene conical cable entry
 - Heat-resistant up to 105°C
- for conductors from 1.5 to 16 mm² (AWG 16-6)
tin-plated copper
dimensional tolerances to DIN 46228 part 4

General ordering data

Version	Wire-end ferrule, Standard, 14 mm, 10 mm, grey
Order No.	9006750000
Type	H4,0/19,5X GR SV
GTIN (EAN)	4008190332297
Qty.	100 pc(s).
Packaging	Multipack bag

H4,0/19,5X GR SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	0.37 g
------------	--------

Technical data

Description of article	Wire end ferrule for short-circuit-proof and earth-fault-proof lines, grey	Version	Standard
------------------------	--	---------	----------

Wire-end ferrules

Collar diameter (D2)	7.8 mm	Colour code	Weidmueller
Conductor cross-section	4 mm ²	Contact surface diameter (D1)	2.9 mm
Contact surface length (L2)	10 mm	L1 in mm	19.5 mm
Metal sleeve thickness (S1)	0.2 mm	Plastic collar thickness (S2)	0.3 mm
Stripping length	14 mm	Wire connection cross section AWG, max.	AWG 12

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

H4,0/19,5X GR SV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

