

LG DMS PRO/ DMS 3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Version	DMS 3, 90 % bei 3x 500 V AC / > 91 % bei 3 x 400 V AC
Order No.	9007460000
Type	LG DMS PRO/ DMS 3
GTIN (EAN)	4008190404970
Qty.	1 pc(s).

LG DMS PRO/ DMS 3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	604.79 g
------------	----------

Technical data

Charging time	Description of article	Mains-operated torque screwdriver with 1/4" drive
30 min		

Electric screwdriver

Battery voltage	3.6 V	Bit holder	1/4" DIN 3126 Form E6.3
Charger input	AC 220-240V~50-60Hz 30W	Charger output	DC 2.8...6V; 4.8A / 30W max.
Charging time	30 min	Idling speed	200 u. 600 min ⁻¹
Max. coupling torque	3 Nm	Rated voltage	3.6 V
Weight	600 g	Weight of charger	600 g

Classifications

ETIM 6.0	EC000359	ETIM 7.0	EC000359
ETIM 8.0	EC000359	ETIM 9.0	EC000359
ECLASS 9.1	21-05-92-01	ECLASS 10.0	21-05-92-01
ECLASS 11.0	21-05-29-01	ECLASS 12.0	21-05-29-01
ECLASS 13.0	21-05-29-01		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	