

**HTG 174****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for coaxial connectors**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

**General ordering data**

Version	Pressing tool, Crimping tool for contacts, Hexagonal crimp
Order No.	<a href="#">9012410000</a>
Type	HTG 174
GTIN (EAN)	4008190009434
Qty.	1 pc(s).

**HTG 174****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Net weight	449 g		

**Technical data**

Description of article	Crimping tool for coaxial connectors BNC, TNC and N / AF 4.52	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

**Description of contact**

Type of contact	Coaxial connector
-----------------	-------------------

**tool data crimping**

Crimping station, width (B 1)	10 mm	Crimping station, width (B 2)	2.3 mm
Crimping type/profile	Hexagonal crimp	Diameter of outer sleeve	5.4 mm
Hexagon AF (A)	4.52 mm	Hexagon spanner width (A 2)	1.72 mm
Internal contact diameter (D)	2 mm		

**Classifications**

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

**Downloads**

User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## HTG 174

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

