

H1,0/18D R**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

General ordering data

Version	Wire-end ferrule, Standard, 15 mm, 12 mm, red
Order No.	9019110000
Type	H1,0/18D R
GTIN (EAN)	4008190174828
Qty.	500 pc(s).
Packaging	loose

H1,0/18D R

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.12 g
------------	--------

Technical data

Description of article	Wire end ferrule with plastic collar, red	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Collar diameter (D2)	3 mm	Colour code	DIN
Conductor cross-section	1 mm ²	Contact surface diameter (D1)	1.4 mm
Contact surface length (L2)	12 mm	L1 in mm	18 mm
Metal sleeve thickness (S1)	0.15 mm	Military designation	T 20A 011 A
Plastic collar thickness (S2)	0.25 mm	Stripping length	15 mm
Wire connection cross section AWG, max.	AWG 17		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

H1,0/18D R**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Drawing**