


**H25,0/36D GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

**General ordering data**

Version	Wire-end ferrule, Standard, 24 mm, 22 mm, yellow
Order No.	<a href="#">9019300000</a>
Type	H25,0/36D GE
GTIN (EAN)	4008190054984
Qty.	50 pc(s).
Packaging	loose

## H25,0/36D GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	1.44 g
------------	--------

## Technical data

Description of article	Wire end ferrule with plastic collar, yellow	Version	Standard
------------------------	--	---------	----------

## Wire-end ferrules

Collar diameter (D2)	11.2 mm	Colour code	DIN
Conductor cross-section	25 mm <sup>2</sup>	Contact surface diameter (D1)	7.3 mm
Contact surface length (L2)	22 mm	L1 in mm	36 mm
Metal sleeve thickness (S1)	0.2 mm	Military designation	T 20A 030 A
Plastic collar thickness (S2)	0.4 mm	Stripping length	24 mm
Wire connection cross section AWG, max.	AWG 3		

## Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

## Environmental Product Compliance

REACH SVHC	/
------------	---

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## H25,0/36D GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Drawing

