


H50,0/36D BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Version	Wire-end ferrule, Standard, 26 mm, 20 mm, blue
Order No.	9019340000
Type	H50,0/36D BL
GTIN (EAN)	4008190067632
Qty.	50 pc(s).
Packaging	loose

H50,0/36D BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	2.8 g
------------	-------

Technical data

Description of article	Wire end ferrule with plastic collar, blue	Version	Standard
------------------------	--------------------------------------------	---------	----------

Wire-end ferrules

Collar diameter (D2)	15 mm	Colour code	DIN
Conductor cross-section	50 mm ²	Contact surface diameter (D1)	10.3 mm
Contact surface length (L2)	20 mm	L1 in mm	36 mm
Metal sleeve thickness (S1)	0.3 mm	Military designation	T 20A 034 A
Plastic collar thickness (S2)	0.5 mm	Stripping length	26 mm
Wire connection cross section AWG, max.	AWG 1		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

H50,0/36D BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

