


**H4,0/18T OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- supplied loose in polybag
- DIN colour code
- other colour code

**General ordering data**

Version	Wire-end ferrule, Standard, 12 mm, 10 mm, orange
Order No.	<a href="#">9021100000</a>
Type	H4,0/18T OR
GTIN (EAN)	4008190061708
Qty.	500 pc(s).
Packaging	loose

## H4,0/18T OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	0.256 g
------------	---------

## Technical data

Description of article	Wire end ferrule with plastic collar, orange	Version	Standard
------------------------	--	---------	----------

## Wire-end ferrules

Collar diameter (D2)	4.8 mm	Colour code	Telemecanique
Conductor cross-section	4 mm <sup>2</sup>	Contact surface diameter (D1)	2.8 mm
Contact surface length (L2)	10 mm	L1 in mm	18 mm
Metal sleeve thickness (S1)	0.2 mm	Military designation	T 20A 023 A
Plastic collar thickness (S2)	0.3 mm	Stripping length	12 mm
Wire connection cross section AWG, max.	AWG 12		

## Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## H4,0/18T OR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Drawing

