

CRIMPFIX LS PZ3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper
Order No.	9025300000
Type	CRIMPFIX LS PZ3
GTIN (EAN)	4008190380335
Qty.	1 pc(s).

CRIMPFIX LS PZ3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	330 mm	Depth (inches)	12.992 inch
Height	460 mm	Height (inches)	18.11 inch
Width	390 mm	Width (inches)	15.354 inch
Net weight	35,000 g		

PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 - 5.5 bar	Consumables	loose cable lugs
Crimping length	6/8/10 mm	Drive	Electropneumatic
Electrical connection	100-240 V / 50/60 Hz / 110 VA	Length of wire-end ferrule	12/14/16 mm
Pulse time	approx. 1 s	Stripping range	0.5 - 2.5 mm ² (~AWG 20-14)
Wire end ferrules cross-section, max.	2.5 mm ²	Wire end ferrules cross-section, min.	0.5 mm ²

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-01
ECLASS 10.0	17-13-01-01	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format