

H1,0/12 GE SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Version	Wire-end ferrule, Standard, 8 mm, 6 mm, yellow
Order No.	9028310000
Type	H1,0/12 GE SV
GTIN (EAN)	4008190902070
Qty.	500 pc(s).
Packaging	Multipack bag

H1,0/12 GE SV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.097 g
------------	---------

Technical data

Description of article	Wire end ferrule with plastic collar, yellow	Version	Standard
------------------------	--	---------	----------

Wire-end ferrules

Collar diameter (D2)	3 mm	Colour code	Weidmueller
Conductor cross-section	1 mm ²	Contact surface diameter (D1)	1.4 mm
Contact surface length (L2)	6 mm	L1 in mm	12 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	8 mm	Wire connection cross section AWG, max.	AWG 17

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01
ECLASS 14.0	27-40-02-01		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Engineering Data	CAD data – STEP
User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format
Brochures	

H1,0/12 GE SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Drawing**