


**H0,5/14D ZH W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

**General ordering data**

Version	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, white
Order No.	<a href="#">9037380000</a>
Type	H0,5/14D ZH W
GTIN (EAN)	4008190492861
Qty.	500 pc(s).
Packaging	loose

## H0,5/14D ZH W

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	0.11 g
------------	--------

## Technical data

Description of article	Twin wire end ferrule, white	Version	Twin wire-end ferrule
------------------------	------------------------------	---------	-----------------------

## Wire-end ferrules

Collar height (A)	5 mm	Collar width (B)	3 mm
Colour code	DIN	Conductor cross-section	0.5 mm <sup>2</sup>
Contact surface diameter (D1)	1.4 mm	Contact surface length (L2)	8 mm
L1 in mm	14 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.3 mm	Stripping length	11 mm
Wire connection cross section AWG, max.	AWG 20		

## Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**H0,5/14D ZH W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Drawing**