

CRIMPER 6 I**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for insulated connectors**

cable lugs, terminal pins, parallel and serial connectors,
plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

General ordering data

Version	Tools, Crimping tool for contacts, 0.25mm ² , 6mm ² , Trapezoidal crimp
Order No.	9040450000
Type	CRIMPER 6 I
GTIN (EAN)	4008190461515
Qty.	1 pc(s).

CRIMPER 6 I**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Net weight	504.57 g		

Technical data

Description of article	Crimping tool for insulated connectors, 0.5-6 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Conductor cross-section, max. AWG	AWG 10	Conductor cross-section, min. AWG	AWG 24
Crimping range, max.	6 mm ²	Crimping range, min.	0.25 mm ²
Type of contact	Insulated connector		

tool data crimping

Crimping type/profile	Trapezoidal crimp	Wire end ferrules cross-section, max.	6 mm ²
Wire end ferrules cross-section, min.	0.25 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012
RoHS Compliance Status	Not affected

Downloads

Catalogues	Catalogues in PDF-format
------------	--