

**CRIMPER 25 N D4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for non-insulated connectors**

Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

**General ordering data**

Version	Tools, Crimping tool for contacts, 10mm <sup>2</sup> , 25mm <sup>2</sup>
Order No.	<a href="#">9040460000</a>
Type	CRIMPER 25 N D4
GTIN (EAN)	4008190461508
Qty.	1 pc(s).

**CRIMPER 25 N D4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	250 mm	Width (inches)	9.842 inch
Net weight	550 g		

**Technical data**

Description of article	Crimping tool for non-insulated connectors, 10-25 mm <sup>2</sup>	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

**Description of contact**

Conductor cross-section, max. AWG	AWG 4	Conductor cross-section, min. AWG	AWG 8
Crimping range, max.	25 mm <sup>2</sup>	Crimping range, min.	10 mm <sup>2</sup>
Type of contact	Uninsulated connection		

**Classifications**

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--