

CRIMPER 25 Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for wire-end ferrules, 6mm ² , 25mm ²
Order No.	9040470000
Type	CRIMPER 25 Z
GTIN (EAN)	4008190461485
Qty.	1 pc(s).

CRIMPER 25 Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	250 mm	Width (inches)	9.842 inch
Net weight	529.57 g		

Technical data

Description of article	(1)Crimping tool	Version	Mechanical, without inter-changeable inserts
------------------------	------------------	---------	--

Description of contact

Crimping range, max.	25 mm ²	Crimping range, min.	6 mm ²
Type of contact	Uninsulated connection		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Important note

Product information	Crimping range 2 (with multiple crimping positions): 10 mm ² , 2 x 4 mm ² , 2 x 6 mm ² Crimping range 4 (with multiple crimping positions): 16 mm ² , 2 x 10 mm ²
---------------------	---

Downloads

Catalogues	Catalogues in PDF-format
------------	--