

CRIMPER 16 Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for wire-end ferrules, 6mm ² , 16mm ² , Trapezoidal crimp
Order No.	9040540000
Type	CRIMPER 16 Z
GTIN (EAN)	4008190461447
Qty.	1 pc(s).

CRIMPER 16 Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	30 mm	Depth (inches)	1.181 inch
Height	78 mm	Height (inches)	3.071 inch
Width	200 mm	Width (inches)	7.874 inch
Length	200 mm	Length (inches)	7.874 inch
Net weight	373.61 g		

Technical data

Description of article	Crimping tool for wire-end ferrules 6 - 16mm ²	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Conductor cross-section, max. AWG	AWG 6	Conductor cross-section, min. AWG	AWG 10
Crimping range, max.	16 mm ²	Crimping range, min.	6 mm ²
Type of contact	Wire-end ferrules with/without plastic collars		

tool data crimping

Crimping type/profile	Trapezoidal crimp	Drive	mechanical
Wire end ferrules cross-section, max.	16 mm ²	Wire end ferrules cross-section, min.	6 mm ²

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Downloads

Catalogues	Catalogues in PDF-format
------------	--