

CUTTER 35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

Version	Cutting tool for one-hand operation
Order No.	9040560000
Type	CUTTER 35
GTIN (EAN)	4008190464943
Qty.	1 pc(s).

CUTTER 35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	40 mm	Depth (inches)	1.575 inch
Height	85 mm	Height (inches)	3.346 inch
Width	290 mm	Width (inches)	11.417 inch
Net weight	599.4 g		

Technical data

Description of article	Front cable cutter up to 35 mm outer diameter	Version	One-hand mechanical
------------------------	---	---------	---------------------

Cutting tools

Aluminium sector cable	4 x 70 SE	Copper cable - flexible, max.	240 mm ²
Copper cable - flexible, max. (kcmil)	500 kcmil	Copper cable - stranded, max.	240 mm ²
Copper cable, max. diameter	35 mm	Copper sector cable	3 x 70 SM
Data / telephone / control cable, max. Ø 35 mm		Stranded aluminium cable, max (mm ²)	240 mm ²
Stranded aluminium cable, max. (kcmil)	500 kcmil	Stranded aluminium cable, max. diameter	35 mm

Classifications

ETIM 6.0	EC000142	ETIM 7.0	EC000142
ETIM 8.0	EC000142	ETIM 9.0	EC000142
ECLASS 9.0	21-04-47-01	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-47-01	ECLASS 11.0	21-04-47-01
ECLASS 12.0	21-04-47-01	ECLASS 13.0	21-04-47-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Downloads

Catalogues	Catalogues in PDF-format
------------	--