

**SE TOP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

**General ordering data**

Version	Diagonal-cutting pliers
Order No.	<a href="#">9046340000</a>
Type	SE TOP
GTIN (EAN)	4032248357642
Qty.	1 pc(s).

**SE TOP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	160 mm	Width (inches)	6.299 inch
Net weight	220 g		

**Technical data**

Description of article	VDE-insulated diagonal-cutting pliers, 145 mm long
------------------------	--

**Pliers**

Conductor diameter, max. (H)	2.5 mm	Conductor diameter, max. (MH)	3.5 mm
Conductor diameter, max. (P)	2 mm	Cutter hardness	64 HRC
Protective insulation, 1000 V	Yes	Shape (diagonal-cutting pliers)	Heavy-duty diagonal-cutting pliers
Total length	160 mm		

**Classifications**

ETIM 6.0	EC000142	ETIM 7.0	EC000142
ETIM 8.0	EC000142	ETIM 9.0	EC000142
ECLASS 9.0	21-04-47-01	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-47-01	ECLASS 11.0	21-04-47-01
ECLASS 12.0	21-04-47-01	ECLASS 13.0	21-04-47-01

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

**Approvals**

Approvals

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	