

**HTF AFK 2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for for turned/stamped contact**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

**General ordering data**

Version	Pressing tool, Crimping tool for contacts, 0.2mm <sup>2</sup> , 2.5mm <sup>2</sup> , B-Crimp
Order No.	<a href="#">9201040000</a>
Type	HTF AFK 2.5
GTIN (EAN)	4032248419678
Qty.	1 pc(s).

**HTF AFK 2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Net weight	533 g		

**Technical data**

Description of article	Crimping tool for AFK flat-blade contacts with opened crimping claws	Version	Mechanical, without interchangeable inserts
------------------------	--	---------	---

**Description of contact**

Conductor cross-section, max. AWG	AWG 12	Conductor cross-section, min. AWG	AWG 24
Crimping range, max.	2.5 mm <sup>2</sup>	Crimping range, min.	0.2 mm <sup>2</sup>
Type of contact	Weidmüller FEKO ZRV		

**tool data crimping**

Crimping type/profile	B-Crimp
-----------------------	---------

**Classifications**

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	21-04-38-11
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012
RoHS Compliance Status	Not affected

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

### HTF AFK 2.5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Similar to illustration

