

WQV PEN 95N/120N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

General ordering data

| | |
|------------|--|
| Version | Cross-connector (terminal), when screwed in, Number of poles: 2, Pitch in mm (P): 27.00, Insulated: No, 269 A, Silver grey |
| Order No. | 9201630000 |
| Type | WQV PEN 95N/120N |
| GTIN (EAN) | 4032248561339 |
| Qty. | 5 pc(s). |

WQV PEN 95N/120N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 65.3 mm | Depth (inches) | 2.571 inch |
| Height | 37 mm | Height (inches) | 1.457 inch |
| Width | 9.5 mm | Width (inches) | 0.374 inch |
| Net weight | 53.2 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|---------------|--------|-------------|
| Material | tinned copper | Colour | Silver grey |
|----------|---------------|--------|-------------|

System specifications

| | |
|---------|-----------------|
| Version | Cross-connector |
|---------|-----------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | when screwed in | Type of mounting | when screwed in |

Cross-connector

| | | | |
|-------------------------------------|-----------------|---------------------------|-------|
| Number of cross-connected terminals | 2 | Rated current, multi-pole | 269 A |
| Type | Cross-connector | | |

Dimensions

| | |
|-----------------|-------|
| Pitch in mm (P) | 27 mm |
|-----------------|-------|

General

| | | | |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 2 |
|---------------------|-----------------|-----------------|---|

Rating data

| | |
|---------------|-------|
| Rated current | 269 A |
|---------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

WQV PEN 95N/120N

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| User Documentation | StorageConditionsTerminalBlocks Instruction User Manual WQV PEN |
| Catalogues | Catalogues in PDF-format |
| Brochures | |