

H0,75/19S ZH W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Polypropylene conical cable entry funnel
 - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm² (AWG 20-7)
Material: E-Cu, tin galvanised
Dimensional tolerance acc. to DIN 46228 sect. 4

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Twin wire-end ferrule, 21 mm, 12 mm, white |
| Order No. | 9202820000 |
| Type | H0,75/19S ZH W |
| GTIN (EAN) | 4032248515769 |
| Qty. | 500 pc(s). |
| Packaging | loose |

H0,75/19S ZH W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | |
|------------|---------|
| Net weight | 0.155 g |
|------------|---------|

Technical data

| | | | |
|------------------------|------------------------------|---------|-----------------------|
| Description of article | Twin wire end ferrule, white | Version | Twin wire-end ferrule |
|------------------------|------------------------------|---------|-----------------------|

Wire-end ferrules

| | | | |
|---|-------------|-----------------------------|----------------------|
| Collar height (A) | 5.5 mm | Collar width (B) | 3 mm |
| Colour code | Weidmueller | Conductor cross-section | 0.75 mm ² |
| Contact surface diameter (D1) | 1.7 mm | Contact surface length (L2) | 12 mm |
| L1 in mm | 19 mm | Metal sleeve thickness (S1) | 0.15 mm |
| Plastic collar thickness (S2) | 0.3 mm | Stripping length | 21 mm |
| Wire connection cross section AWG, max. | AWG 18 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ECLASS 9.0 | 27-40-02-01 | ECLASS 9.1 | 27-40-02-01 |
| ECLASS 10.0 | 27-40-02-01 | ECLASS 11.0 | 27-40-02-01 |
| ECLASS 12.0 | 27-40-02-01 | ECLASS 13.0 | 27-40-02-01 |
| ECLASS 14.0 | 27-40-02-01 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E354986 |

Downloads

| | |
|--------------------|--|
| Engineering Data | CAD data – STEP |
| User Documentation | Technical information - EN Technical information - DE |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

H0,75/19S ZH W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Drawings****Drawing**