

KOBBS 9.5X50

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Overpressure valve protects against overloading
- Cylinder head angled at 90°
- Angled head can be rotated through 360°
- Ergonomic handle springs back automatically
- The waste piece no longer becomes jammed thanks to triple splitting
- Hydraulic punch made of high-strength aluminium (approx. 40% weight saving)
- Service life greatly reduced when stainless steel sheets are used

General ordering data

| | |
|------------|----------------------------|
| Version | Sheet holes |
| Order No. | 9205030000 |
| Type | KOBBS 9.5X50 |
| GTIN (EAN) | 4032248694266 |
| Qty. | 1 pc(s). |

KOBBS 9.5X50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|----------|--------|-----------------|------------|
| Height | 50 mm | Height (inches) | 1.969 inch |
| Diameter | 9.5 mm | Net weight | 63 g |

Technical data

| | |
|------------------------|---|
| Description of article | Tension screw with bearings 9.5 x 50.0 mm |
|------------------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000149 | ETIM 7.0 | EC000149 |
| ETIM 8.0 | EC000149 | ETIM 9.0 | EC000149 |
| ECLASS 9.0 | 21-04-50-03 | ECLASS 9.1 | 21-01-92-90 |
| ECLASS 10.0 | 21-04-50-03 | ECLASS 11.0 | 21-04-50-03 |
| ECLASS 12.0 | 21-04-50-03 | ECLASS 13.0 | 21-04-50-03 |
| ECLASS 14.0 | 21-04-50-03 | | |

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 6a3438d7-aa8c-48e4-8879-adf736ca79e3 |
| RoHS Compliance Status | Not affected |

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
| Brochures | |