

KOBBS 19X55**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Overpressure valve protects against overloading
- Cylinder head angled at 90°
- Angled head can be rotated through 360°
- Ergonomic handle springs back automatically
- The waste piece no longer becomes jammed thanks to triple splitting
- Hydraulic punch made of high-strength aluminium (approx. 40% weight saving)
- Service life greatly reduced when stainless steel sheets are used

General ordering data

Version	Sheet holes
Order No.	9205040000
Type	KOBBS 19X55
GTIN (EAN)	4032248694273
Qty.	1 pc(s).

KOBBS 19X55**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	55 mm	Height (inches)	2.165 inch
Diameter	19 mm	Net weight	245 g

Technical data

Description of article	Tension screw with bearings 19.0 x 55.0 mm
------------------------	--

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-01-92-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-04-50-03
ECLASS 12.0	21-04-50-03	ECLASS 13.0	21-04-50-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6a3438d7-aa8c-48e4-8879-adf736ca79e3

Downloads

Catalogues	Catalogues in PDF-format
Brochures	