

**POK MOPL 1212****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

**General ordering data**

|            |   |
|------------|---|
| Version    | Klippon POK (polyester empty enclosure), Mounting plate, Height: 107 mm, Width: 109 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, Miscellaneous, silver |
| Order No.  | <a href="#">9510590000</a>  |
| Type       | POK MOPL 1212   |
| GTIN (EAN) | 4008190498221   |
| Qty.       | 1 pc(s).  |

**POK MOPL 1212****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|                             |        |                            |            |
|-----------------------------|--------|----------------------------|------------|
| Depth                       | 1.5 mm | Depth (inches)             | 0.059 inch |
| Height                      | 107 mm | Height (inches)            | 4.213 inch |
| Width                       | 109 mm | Width (inches)             | 4.291 inch |
| Mounting dimension - height | 52 mm  | Mounting dimension - width | 95 mm      |
| Net weight                  | 119 g  |                            |            |

**General information**

|                |                         |                    |                 |
|----------------|-------------------------|--------------------|-----------------|
| Material       | Sheet steel, galvanized | Material thickness | 1.5 mm          |
| Surface finish | Miscellaneous           | Type of fixing     | when screwed in |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000213    | ETIM 7.0    | EC000213    |
| ETIM 8.0    | EC000213    | ETIM 9.0    | EC000213    |
| ECLASS 9.0  | 27-40-06-39 | ECLASS 9.1  | 27-18-92-90 |
| ECLASS 10.0 | 27-40-06-39 | ECLASS 11.0 | 27-40-06-39 |
| ECLASS 12.0 | 27-40-06-39 | ECLASS 13.0 | 27-40-06-39 |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |

**POK MOPL 1212****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Depth 7.5 mm**

The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

**General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | TS35X7.5 ST K41            | Version  |
| Order No.  | <a href="#">8000003439</a> | Rail, TS 35, TS 35 x 7.5, Width: 105 mm, without slot, Steel, galvanic |
| GTIN (EAN) | 4050118652628              | zinc plated and passivated   |
| Qty.       | 20 pc(s).                  |  |