

STRIPPER ROUND TOP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

General ordering data

Version	Sheathing strippers
Order No.	9918050000
Type	STRIPPER ROUND TOP
GTIN (EAN)	4032248359165
Qty.	1 pc(s).

STRIPPER ROUND TOP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	25 mm	Depth (inches)	0.984 inch
Height	35 mm	Height (inches)	1.378 inch
Width	125 mm	Width (inches)	4.921 inch
Net weight	46.2 g		

Technical data

Description of article	Junction box sheathing stripper with individual core stripping unit and longitudinal cutter
------------------------	---

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	0.2 mm ²	Max. conductor diameter	13 mm
Min. conductor diameter	8 mm	Stripping range, min.	0.25 mm ²

Classifications

ETIM 6.0	EC000163	ETIM 7.0	EC000163
ETIM 8.0	EC000163	ETIM 9.0	EC000163
ECLASS 9.0	21-04-90-90	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-90-90	ECLASS 11.0	21-04-90-90
ECLASS 12.0	21-04-90-90	ECLASS 13.0	21-04-90-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

STRIPPER ROUND TOP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

