

**STRIPPER ROUND TOP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm<sup>2</sup> to 5 x 2.5 mm<sup>2</sup>
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

**General ordering data**

Version	Sheathing strippers
Order No.	<a href="#">9918050000</a>
Type	STRIPPER ROUND TOP
GTIN (EAN)	4032248359165
Qty.	1 pc(s).

**STRIPPER ROUND TOP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	25 mm	Depth (inches)	0.984 inch
Height	35 mm	Height (inches)	1.378 inch
Width	125 mm	Width (inches)	4.921 inch
Net weight	46.2 g		

**Technical data**

Description of article	Junction box sheathing stripper with individual core stripping unit and longitudinal cutter
------------------------	---

**Stripping tools**

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	0.2 mm <sup>2</sup>	Max. conductor diameter	13 mm
Min. conductor diameter	8 mm	Stripping range, min.	0.25 mm <sup>2</sup>

**Classifications**

ETIM 6.0	EC000163	ETIM 7.0	EC000163
ETIM 8.0	EC000163	ETIM 9.0	EC000163
ECLASS 9.0	21-04-90-90	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-90-90	ECLASS 11.0	21-04-90-90
ECLASS 12.0	21-04-90-90	ECLASS 13.0	21-04-90-90

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0
RoHS Compliance Status	Not affected

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**STRIPPER ROUND TOP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

