

## FF-FIMT 4X 54

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

## Általános rendelési adatok

Változat	Filter mat, IP54, fehér
Rendelési szám	<a href="#">2556790000</a>
Típus	FF-FIMT 4X 54
GTIN (EAN)	4050118567410
Qty.	5 Stück

## FF-FIMT 4X 54

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Műszaki adatok

## Méretek és tömegek

Magasság	216 mm	Magasság (coll)	8,504 inch
Szélesség	216 mm	Szélesség (coll)	8,504 inch
Nettó tömeg	13,2 g		

## Hőmérsékletek

Üzemi hőmérsékleti tartomány	-40...55 °C
------------------------------	-------------

## General data

Felszerelés típusa	Felpattintható	Filter class	G 4
Protection class (UL)	Type 12	Szín	fehér
With filter	Igen	Üzemi hőmérsékleti tartomány	-40...55 °C

## Besorolások

ETIM 6.0	EC002513	ETIM 7.0	EC002513
ETIM 8.0	EC002513	ETIM 9.0	EC002513
ECLASS 9,1	27-18-07-06	ECLASS 10.0	27-18-07-06
ECLASS 11.0	27-18-07-06	ECLASS 12.0	27-18-07-06
ECLASS 13.0	27-18-07-06		

## Tanúsítványok

ROHS	Megfelel
------	----------

## Letöltések

User Documentation	<a href="#">Operating instructions</a>
Katalógusok	<a href="#">Catalogues in PDF-format</a>