

RFF-FIMT 605X 54

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

Általános rendelési adatok

Verzió	Filter mat, IP54, fehér
Rendelési szám	2557750000
Típus	RFF-FIMT 605X 54
GTIN (EAN)	4050118568394
Qty.	20 Stück

RFF-FIMT 605X 54

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Műszaki adatok

Méretetek és tömegek

Magasság	70 mm	Magasság (coll)	2,756 inch
Szélesség	290 mm	Szélesség (coll)	11,417 inch
Nettó tömeg	17,35 g		

Hőmérsékletek

Üzemi hőmérsékleti tartomány	-15...55 °C
------------------------------	-------------

General data

Felszerelés típusa	becsavart állapotban	Filter class	G 4
Protection class (UL)	Type 12	Szín	fehér
Üzemi hőmérsékleti tartomány	-15...55 °C		

Besorolások

ETIM 6.0	EC000320	ETIM 7.0	EC000320
ETIM 8.0	EC000320	ETIM 9.0	EC000320
ECLASS 9,1	27-18-07-16	ECLASS 10.0	27-18-07-16
ECLASS 11.0	27-18-07-16	ECLASS 12.0	27-18-07-16
ECLASS 13.0	27-18-07-16		

Tanúsítványok

ROHS	Megfelel
------	----------

Letöltések

User Documentation	Operating instructions
Katalógusok	Catalogues in PDF-format