

FUSE WSFL 10X85 30A 1K5V GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

gPV 10×85 cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards).

Ogólne dane zamówieniowe

Wersja	Fotowoltaika, Wkładka bezpiecznika topikowego, 1500 V, 10x85, gPV, 30 A
Nr zam.	4000005431
Typ	FUSE WSFL 10X85 30A 1K5V GPV
GTIN (EAN)	8430243440424
Ilość	50 Szt.

FUSE WSFL 10X85 30A 1K5V GPV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Dane techniczne****Wymiary i ciężary**

Wysokość	85 mm	Wysokość (cale)	3,346 inch
Szerokość	10,3 mm	Szerokość (cale)	0,406 inch
Masa netto	0,2 g		

Wkładka bezpiecznika

Standardowy bezpiecznik topikowy	IEC 60269-6, gPV (EN 60269-6)	Prąd	30 A
Znamionowe napięcie stałe	1 500 V	Wymiarowana zdolność wyłączeniowa	10 kA
materiał styki	srebrzone	Rozpraszanie mocy, maks.	5,5 W

Klasyfikacje

ETIM 7.0	EC002704	ETIM 8.0	EC002704
ETIM 9.0	EC002704	ECLASS 11.0	27-14-20-02
ECLASS 12.0	27-14-20-02	ECLASS 13.0	27-14-20-02

Dopuszczenia

ROHS	Zgodny
------	--------

Pobieranie

Katalogi	Catalogues in PDF-format
----------	--