


AP SAK4-10 KRG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

Version	End plate (terminals), 40 mm x 1.5 mm, dark beige, yellow
Order No.	0117920000
Type	AP SAK4-10 KRG
GTIN (EAN)	4008190135904
Qty.	20 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2022-12-31
Alternative product	1050000000

AP SAK4-10 KRG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	36 mm	Depth (inches)	1.417 inch
Height	40 mm	Height (inches)	1.575 inch
Width	1.5 mm	Width (inches)	0.059 inch
Net weight	3.3 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	KrG	Colour	dark beige, yellow
UL 94 flammability rating	V-0		

System specifications

Version	End plate
---------	-----------

Additional technical data

Installation advice	Direct mounting	Snap-on	Yes
---------------------	-----------------	---------	-----

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ETIM 9.0	EC000886
ECLASS 9.1	27-14-11-33	ECLASS 10.0	27-14-11-33
ECLASS 11.0	27-14-11-33	ECLASS 12.0	27-14-11-33
ECLASS 13.0	27-25-03-01		

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format