

**H6,0/15****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in polybag

**General ordering data**

Version	Wire-end ferrule, Standard, 15 mm, 15 mm, No
Order No.	<a href="#">0124700000</a>
Type	H6,0/15
GTIN (EAN)	4008190003807
Qty.	500 pc(s).
Packaging	loose

**H6,0/15****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight	0.302 g
------------	---------

**Technical data**

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	-----------------------------------------	---------	----------

**Wire-end ferrules**

Collar diameter (D2)	4.7 mm	Conductor cross-section	6 mm <sup>2</sup>
Contact surface diameter (D1)	3.5 mm	Contact surface length (L2)	15 mm
L1 in mm	15 mm	Stripping length	15 mm
Wire connection cross section AWG, max.	AWG 10		

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**H6,0/15**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

