

QL 2 SAK4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

| | |
|------------|---|
| Version | Cross-connector (terminal), when screwed in, Number of poles: 2, Pitch in mm (P): 6.00, Insulated: No, 41 A, grey |
| Order No. | 0130600000 |
| Type | QL 2 SAK4 |
| GTIN (EAN) | 4008190077372 |
| Qty. | 100 pc(s). |

QL 2 SAK4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.6 mm | Depth (inches) | 0.024 inch |
| Height | 6 mm | Height (inches) | 0.236 inch |
| Width | 11.5 mm | Width (inches) | 0.453 inch |
| Net weight | 0.26 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|--------|--------|------|
| Material | Copper | Colour | grey |
|----------|--------|--------|------|

System specifications

| | |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | when screwed in | | |

Cross-connector

| | | | |
|-------------------------------------|------|-----------------------|-----------------|
| Number of cross-connected terminals | 2 | Rated current, 2-pole | 32 A |
| Rated current, multi-pole | 32 A | Type | Cross-connector |

Dimensions

| | |
|-----------------|------|
| Pitch in mm (P) | 6 mm |
|-----------------|------|

General

| | | | |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 2 |
|---------------------|-----------------|-----------------|---|

Rating data

| | |
|---------------|------|
| Rated current | 41 A |
|---------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

QL 2 SAK4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

QL 2 SAK4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****QL mounting screws**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

| | | |
|------------|----------------------------|--------------------------------------|
| Type | KISC M3X20.5/10 EK4 | Version |
| Order No. | 0303000000 | Clamping yoke, Mounting screw, Steel |
| GTIN (EAN) | 4008190163686 | |
| Qty. | 100 pc(s). | |