

QB 25/6.5/11.5 SAKR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Cross-connector (terminal), when screwed in, Number of poles: 25, Pitch in mm (P): 6.50, Insulated: No, 32 A, grey
Order No.	0134000000
Type	QB 25/6.5/11.5 SAKR
GTIN (EAN)	4008190118945
Qty.	20 pc(s).

QB 25/6.5/11.5 SAKR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	13.24 mm	Depth (inches)	0.521 inch
Height	158.6 mm	Height (inches)	6.244 inch
Width	0.9 mm	Width (inches)	0.035 inch
Net weight	7.852 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Cu Zn	Colour	grey
----------	-------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
Type of mounting	when screwed in		

Cross-connector

Type	Cross-connector
------	-----------------

Dimensions

Pitch in mm (P)	6.5 mm
-----------------	--------

General

Installation advice	Direct mounting	Number of poles	25
---------------------	-----------------	-----------------	----

Rating data

Rated current	32 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format