

VH 13.5/4.9/3.3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

General ordering data

Version	Connecting sleeve (terminal), Height: 4.9 mm, Width: 4.9 mm, Depth: 13.5 mm, Copper
Order No.	0248500000
Type	VH 13.5/4.9/3.3
GTIN (EAN)	4008190022723
Qty.	100 pc(s).

VH 13.5/4.9/3.3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	13.5 mm	Depth (inches)	0.531 inch
Height	4.9 mm	Height (inches)	0.193 inch
Width	4.9 mm	Width (inches)	0.193 inch
Diameter	4.9 mm	Net weight	0.9 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Copper	Colour	grey
----------	--------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	1	Type	Cross-connector
-------------------------------------	---	------	-----------------

Dimensions

Diameter	4.9 mm	TS 32 offset	32.5 mm
----------	--------	--------------	---------

General

Installation advice	Direct mounting	Number of poles	1
---------------------	-----------------	-----------------	---

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	