

CLI C 1-6 GE/SW 73 MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 2.5 - 5 mm, 6 x 4.2 mm, yellow |
| Order No. | 0252711594 |
| Type | CLI C 1-6 GE/SW 73 MP |
| GTIN (EAN) | 4008190014582 |
| Qty. | 100 pc(s). |

CLI C 1-6 GE/SW 73 MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 5 mm | Depth (inches) | 0.197 inch |
| Height | 6 mm | Height (inches) | 0.236 inch |
| Width | 4.2 mm | Width (inches) | 0.165 inch |
| Net weight | 0.11 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

General data

| | | |
|--|--|----------------|
| Colour | yellow | |
| Colour of printing | black | |
| Halogen | Yes | |
| Insulation cross-section, max. | 5 | |
| Material | PVC, soft, without Cadmium | |
| Material colour according to resistance code | 4 | |
| Number of markers per combination | 1 Component part = Conductor and cable markers | |
| Number of markers per packaging unit | Form of supply | Component part |
| Operating temperature range | -30...80 °C | |
| Operating temperature range, max. | 80 °C | |
| Operating temperature range, min. | -30 °C | |
| Orientation of print | horizontal | |
| Printed characters | Numbers | |
| Printing | 73 | |
| Printing method | hot-embossing | |
| Recommended industries | Process, Machinery | |
| Type of printing | Standard | |
| UL 94 flammability rating | V-0 | |
| Version | MultiPack | |
| Width | 4.2 mm | |

Conductor and cable markers

| | | | |
|-------------------------------|---------------------|----------------------------------|-------------------------|
| Conductor O.D. | 2.5 - 5 mm | Conductor O.D., max. | 5 mm |
| Conductor O.D., min. | 2.5 mm | Conductor cross-section, max. | 4 mm ² |
| Conductor cross-section, min. | 1.5 mm ² | Cross-section for connected wire | 1.5 - 4 mm ² |
| Halogen | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

CLI C 1-6 GE/SW 73 MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Product Change Notification

[PCN CableLine_DE](#)

[PCN CableLine_EN](#)

Catalogues

[Catalogues in PDF-format](#)

CLI C 1-6 GE/SW 73 MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



Similar to illustration