

**VH 4.9/4/2.8****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	Connecting sleeve (terminal), Height: 4 mm, Width: 4 mm, Depth: 5 mm, Copper
Order No.	<a href="#">0296800000</a>
Type	VH 4.9/4/2.8
GTIN (EAN)	4008190008000
Qty.	100 pc(s).

## VH 4.9/4/2.8

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	5 mm	Depth (inches)	0.197 inch
Height	4 mm	Height (inches)	0.157 inch
Width	4 mm	Width (inches)	0.157 inch
Diameter	4 mm	Net weight	0.26 g

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Material	Copper	Colour	grey
----------	--------	--------	------

## System specifications

Version	for cross-connection link
---------	---------------------------

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

## Cross-connector

Number of cross-connected terminals	1	Type	Cross-connector
-------------------------------------	---	------	-----------------

## Dimensions

Diameter	4 mm
----------	------

## General

Installation advice	Direct mounting
---------------------	-----------------

## Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>