

SH 1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Busbar support
Order No.	0299860000
Type	SH 1
GTIN (EAN)	4008190135133
Qty.	20 pc(s).

SH 1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	24 mm	Depth (inches)	0.945 inch
Height	24.5 mm	Height (inches)	0.965 inch
Width	26 mm	Width (inches)	1.024 inch
Net weight	2 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Polyamide 66	Surface finish	all others
Colour	beige	UL 94 flammability rating	V-2

Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in
---------------------	-----------------	------------------	-----------------

Conductors for clamping (rated connection)

Type of connection	Miscellaneous
--------------------	---------------

General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
Surface finish	all others		

Classifications

ETIM 6.0	EC001166	ETIM 7.0	EC001166
ETIM 8.0	EC001166	ETIM 9.0	EC001166
ECLASS 9.0	27-40-06-07	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-40-06-07	ECLASS 11.0	27-40-06-07
ECLASS 12.0	27-40-06-07	ECLASS 13.0	27-40-06-07

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – 02961_SH_1_DXF.dxf CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	