

VH 27/5/3.4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

General ordering data

Version	Connecting sleeve (terminal), Height: 5 mm, Width: 5 mm, Depth: 27 mm, Cu Zn
Order No.	0309400000
Type	VH 27/5/3.4
GTIN (EAN)	4008190143176
Qty.	50 pc(s).

VH 27/5/3.4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	27 mm	Depth (inches)	1.063 inch
Height	5 mm	Height (inches)	0.197 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	2.434 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Cu Zn	Colour	grey
----------	-------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	1	Type	Cross-connector
-------------------------------------	---	------	-----------------

General

Installation advice	Direct mounting	Number of poles	1
---------------------	-----------------	-----------------	---

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	73c55621-8329-401d-bde2-7fd78e0e60e4

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format