

**QL 10 SAK35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 10, Pitch in mm (P): 18.00, Insulated: No, 99 A, grey
Order No.	<a href="#">0338600000</a>
Type	QL 10 SAK35
GTIN (EAN)	4008190106133
Qty.	20 pc(s).

**QL 10 SAK35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	3 mm	Depth (inches)	0.118 inch
Height	8 mm	Height (inches)	0.315 inch
Width	171.4 mm	Width (inches)	6.748 inch
Net weight	30.35 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	Cu Zn	Colour	grey
----------	-------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

**Cross-connector**

Number of cross-connected terminals	10	Rated current, 2-pole	110 A
Rated current, multi-pole	99 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	18 mm
-----------------	-------

**General**

Installation advice	Direct mounting	Number of poles	10
---------------------	-----------------	-----------------	----

**Rating data**

Rated current	99 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Approvals**

ROHS	Conform
------	---------

## QL 10 SAK35

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**QL 10 SAK35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Miscellaneous**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Type	SS M4 D 128-A 4	Version
Order No.	<a href="#">0136400000</a>	Lock washer, Copper
GTIN (EAN)	4008190118143	
Qty.	100 pc(s).	

**Screws**

Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

**General ordering data**

Type	BFSC M4X30	Version
Order No.	<a href="#">0267100000</a>	Mounting screw (Terminal)
GTIN (EAN)	4008190187897	
Qty.	50 pc(s).	

**QL 10 SAK35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Connection sleeves****General ordering data**

Type	VH 17/8.2/5.2	Version
Order No.	<a href="#">0267000000</a>	Connecting sleeve (terminal), Height: 8 mm, Width: 8 mm, Depth: 17
GTIN (EAN)	4008190146986	mm, Cu Zn
Qty.	50 pc(s).	