

QB 58/8/9/WI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Cross-connector (terminal), when screwed in, Number of poles: 58, Pitch in mm (P): 8.00, Insulated: No, 27 A, grey
Order No.	0545300000
Type	QB 58/8/9/WI
GTIN (EAN)	4008190125080
Qty.	10 pc(s).

QB 58/8/9/WI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	17.5 mm	Depth (inches)	0.689 inch
Height	458.5 mm	Height (inches)	18.051 inch
Width	0.8 mm	Width (inches)	0.031 inch
Net weight	22.1 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-60 °C...130 °C
---------------------	----------------	-----------------------	-----------------

Material data

Material	Copper	Colour	grey
----------	--------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	58	Type	Cross-connector
-------------------------------------	----	------	-----------------

Dimensions

Pitch in mm (P)	8 mm
-----------------	------

General

Installation advice	Direct mounting	Number of poles	58
---------------------	-----------------	-----------------	----

Rating data

Rated current	27 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform
------	---------

QB 58/8/9/WI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

QB 58/8/9/WI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Insulation profiles****General ordering data**

Type	ISPF QB58 BL	Version
Order No.	0546080000	Insulation profile, PVC, blue
GTIN (EAN)	4008190927035	
Qty.	10 pc(s).	
Type	ISPF QB58 SW	Version
Order No.	0546000000	Insulation profile, PVC, black
GTIN (EAN)	4008190116705	
Qty.	10 pc(s).	
Type	ISPF QB58 RT	Version
Order No.	0546040000	Insulation profile, PVC, red
GTIN (EAN)	4008190497941	
Qty.	10 pc(s).	