

**QB 58/8/15****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 58, Pitch in mm (P): 8.00, Insulated: No, 27 A, grey
Order No.	<a href="#">0545400000</a>
Type	QB 58/8/15
GTIN (EAN)	4008190028794
Qty.	10 pc(s).

QB 58/8/15

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	17.5 mm	Depth (inches)	0.689 inch
Height	458.5 mm	Height (inches)	18.051 inch
Width	0.8 mm	Width (inches)	0.031 inch
Net weight	21.96 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-60 °C...130 °C
---------------------	----------------	-----------------------	-----------------

### Material data

Material	Copper	Colour	grey
----------	--------	--------	------

### System specifications

Version	for cross-connection link
---------	---------------------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

### Cross-connector

Number of cross-connected terminals	58	Rated current, multi-pole	17.5 A
Type	Cross-connector		

### Dimensions

Pitch in mm (P)	8 mm
-----------------	------

### General

Installation advice	Direct mounting	Number of poles	58
---------------------	-----------------	-----------------	----

### Rating data

Rated current	27 A
---------------	------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

### Approvals

ROHS	Conform
------	---------

**QB 58/8/15**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**QB 58/8/15****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Insulation profiles****General ordering data**

Type	ISPF QB58 SW	Version
Order No.	<a href="#">0546000000</a>	Insulation profile, PVC, black
GTIN (EAN)	4008190116705	
Qty.	10 pc(s).	
Type	ISPF QB58 RT	Version
Order No.	<a href="#">0546040000</a>	Insulation profile, PVC, red
GTIN (EAN)	4008190497941	
Qty.	10 pc(s).	
Type	ISPF QB58 BL	Version
Order No.	<a href="#">0546080000</a>	Insulation profile, PVC, blue
GTIN (EAN)	4008190927035	
Qty.	10 pc(s).	