

**G 25/0.25A/M GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

For protection against overcurrent, we offer cartridge fuse with dimensions 5x25 mm in sizes from 250 mA to 6.3 A.

**General ordering data**

Version	Miniature fuse, medium time-lag, 0.25 A, G-Si. 5 x 25
Order No.	<a href="#">0546900000</a>
Type	G 25/0.25A/M GE
GTIN (EAN)	4008190097370
Qty.	10 pc(s).

**G 25/0.25A/M GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	5 mm	Depth (inches)	0.197 inch
Height	25 mm	Height (inches)	0.984 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	1.1 g		

**Material data**

Colour	Light Grey
--------	------------

**System specifications**

Version	Fuse accessories
---------	------------------

**Fuse cartridges**

Cartridge fuse	G-Si. 5 x 25	Characteristics	medium time-lag
Colour	Light Grey	Colour of the indicator	yellow
Current	0.25 A	Melting integral	0.22 A²s
Optical function display	Yes	Power output (@ 1.5 In)	0.2 W
Rated breaking capacity	80 A	Version	Fuse accessories
Voltage drop	375 mV		

**Rating data**

Rated voltage	250 V	Rated current	0.25 A
---------------	-------	---------------	--------

**Classifications**

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ETIM 9.0	EC002704
ECLASS 9.0	27-14-20-01	ECLASS 9.1	27-14-20-01
ECLASS 10.0	27-14-20-01	ECLASS 11.0	27-14-20-01
ECLASS 12.0	27-14-20-01	ECLASS 13.0	27-14-20-01

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	