

**CLI O 10-3 GE/SW 5 MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm<sup>2</sup> to max. 4.0 mm<sup>2</sup>. The shape and design guarantee secure and permanent attachment of the individually combinable markers.

**Advantages:**

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

**General ordering data**

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 2 - 3 mm, 3 x 4 mm, yellow |
| Order No.  | <a href="#">0648001517</a>   |
| Type       | CLI O 10-3 GE/SW 5 MP  |
| GTIN (EAN) | 4008190156008  |
| Qty.       | 200 pc(s).   |

**CLI O 10-3 GE/SW 5 MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 4 mm    | Depth (inches)  | 0.157 inch |
| Height     | 3 mm    | Height (inches) | 0.118 inch |
| Width      | 4 mm    | Width (inches)  | 0.157 inch |
| Net weight | 0.025 g |                 |            |

**Temperatures**

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

**General data**

|  |                    |                                   |                            |
|--|--------------------|-----------------------------------|----------------------------|
| Colour                                       | yellow             | Colour of printing                | black                      |
| Halogen                                      | Yes                | Material                          | PVC, soft, without Cadmium |
| Material colour according to resistance code | 4                  | Operating temperature range       | -30...80 °C                |
| Operating temperature range, max.            | 80 °C              | Operating temperature range, min. | -30 °C                     |
| Orientation of print                         | horizontal         | Printed characters                | Numbers                    |
| Printing                                     | 5                  | Printing method                   | hot-embossing              |
| Recommended industries                       | Process, Machinery | Type of printing                  | Standard                   |
| UL 94 flammability rating                    | V-0                | Version                           | MultiPack                  |
| Width  | 4 mm               |                                   |                            |

**Conductor and cable markers**

|                               |                     |                                  |                           |
|-------------------------------|---------------------|----------------------------------|---------------------------|
| Conductor O.D.                | 2 - 3 mm            | Conductor O.D., max.             | 3 mm                      |
| Conductor O.D., min.          | 2 mm                | Conductor cross-section, max.    | 1.5 mm <sup>2</sup>       |
| Conductor cross-section, min. | 0.4 mm <sup>2</sup> | Cross-section for connected wire | 0.4 - 1.5 mm <sup>2</sup> |
| Halogen                       | Yes                 |                                  |                           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|

### CLI O 10-3 GE/SW 5 MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



Similar to illustration