

KSP L80 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	KSP (Klippon shroud), Protective cap, Silicone
Order No.	0930700007
Type	KSP L80 S
GTIN (EAN)	4032248976027
Qty.	10 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2023-07-30

KSP L80 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	120 mm	Height (inches)	4.724 inch
Length	150 mm	Length (inches)	5.905 inch
Net weight	54.6 g		

Temperatures

Operating temperature	-60 °C...200 °C
-----------------------	-----------------

General information

Gap, internal dimension B	85 mm	Halogen	halogen-free
Hardness (IRHD)	60	Inside diameter D2	80 mm
Material	Silicone	O.D.	84 mm
Operating temperature range, max.	200 °C	Operating temperature range, min.	-60 °C
Silicone	Yes	Thickness	2 mm

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

KSP L80 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

