

## HDC 16B DODQ 2QB

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

### General ordering data

|            |  |
|------------|--|
| Version    | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cover for lower part of housing, Side-locking clamp on upper side, Standard |
| Order No.  | <a href="#">1009090000</a>   |
| Type       | HDC 16B DODQ 2QB   |
| GTIN (EAN) | 4032248713837  |
| Qty.       | 1 pc(s).   |

## HDC 16B DODQ 2QB

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Height     | 17 mm | Height (inches) | 0.669 inch |
| Width      | 55 mm | Width (inches)  | 2.165 inch |
| Net weight | 150 g |                 |            |

### Temperatures

|                   |                   |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

### Dimensions

|                      |           |                     |       |
|----------------------|-----------|---------------------|-------|
| Cable entry          | For bases | Height of housing B | 17 mm |
| Total length housing | 93.3 mm   | Width housing C     | 43 mm |

### General data

|                             |                             |                       |                             |
|-----------------------------|-----------------------------|-----------------------|-----------------------------|
| EMC housings                | No                          | Housing main material | diecast aluminium           |
| Material of locking element | Stainless steel, rust-proof | Protection degree     | IP65 (in plugged condition) |
| Surface finish              | Powder coating              |                       |                             |

### Version

|                          |                                  |                          |                                 |
|--------------------------|----------------------------------|--------------------------|---------------------------------|
| BG                       | 6                                | Cable entry              | For bases                       |
| Clamp version            | Side-locking clamp               | Colour (RAL)             | RAL 7035                        |
| Design                   | Standard                         | Design of housing        | Cover for lower part of housing |
| Design of locking system | Side-locking clamp on upper side | Size                     | 6                               |
| Suitable for ModuPlug®   | Yes                              | Top part/bottom part/lid | Cover                           |
| Type                     | Cover                            |                          |                                 |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000437    | ETIM 7.0    | EC000437    |
| ETIM 8.0    | EC000437    | ETIM 9.0    | EC000437    |
| ECLASS 9.0  | 27-44-02-02 | ECLASS 9.1  | 27-44-02-02 |
| ECLASS 10.0 | 27-44-02-02 | ECLASS 11.0 | 27-44-02-02 |
| ECLASS 12.0 | 27-44-02-02 | ECLASS 13.0 | 27-44-02-02 |

|                     |                         |
|---------------------|-------------------------|
| Substance           | Acetone                 |
| Chemical resistance | Conditionally resistant |
| Substance           | Drilling oil            |
| Chemical resistance | Resistant               |
| Substance           | Diesel                  |
| Chemical resistance | Resistant               |
| Substance           | Ethyl alcohol           |
| Chemical resistance | Resistant               |
| Substance           | Transmission oil        |
| Chemical resistance | Resistant               |
| Substance           | Hydraulic oil           |

Creation date April 28, 2024 6:56:09 PM CEST

**HDC 16B DODQ 2QB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data**

|                     |                         |
|---------------------|-------------------------|
| Chemical resistance | Resistant               |
| Substance           | Coolant                 |
| Chemical resistance | Resistant               |
| Substance           | Petroleum benzine       |
| Chemical resistance | Resistant               |
| Substance           | Sweat                   |
| Chemical resistance | Resistant               |
| Substance           | Premium gasoline        |
| Chemical resistance | Conditionally resistant |
| Substance           | Water                   |
| Chemical resistance | Resistant               |
| Substance           | UV                      |
| Chemical resistance | Unstable                |
| Substance           | Ozone                   |
| Chemical resistance | Unstable                |

**Environmental Product Compliance**

|                     |  |
|---------------------|--|
| REACH SVHC          | Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3  |
| SCIP                | e98b2b24-ba23-41bf-8d19-0dda3647412f   |
| Chemical resistance | de.myview.objectmodel.impl.BlockImpl@6ba2af1d de.myview.objectmodel.impl.BlockImpl@5fe18fab<br>de.myview.objectmodel.impl.BlockImpl@6e366c19 de.myview.objectmodel.impl.BlockImpl@574b6754<br>de.myview.objectmodel.impl.BlockImpl@29efe0e7 de.myview.objectmodel.impl.BlockImpl@7aa0bea6<br>de.myview.objectmodel.impl.BlockImpl@27ab434f de.myview.objectmodel.impl.BlockImpl@2b56f129<br>de.myview.objectmodel.impl.BlockImpl@7d68d47c de.myview.objectmodel.impl.BlockImpl@24200f9<br>de.myview.objectmodel.impl.BlockImpl@7f8e8ac5 de.myview.objectmodel.impl.BlockImpl@634de3a4<br>de.myview.objectmodel.impl.BlockImpl@58bd1085 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">Manufacturer's declaration</a>   |
| Engineering Data                            | <a href="#">CAD data – STEP</a>  |
| Product Change Notification                 | <a href="#">20220214 Technical change to HDC housings</a><br><a href="#">20220214 Technische Änderung bei HDC-Gehäusen</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |
| Brochures                                   | <a href="#">FL FIELDWIRING EN</a><br><a href="#">FL FIELDWIRING EN</a>   |

## HDC 16B DODQ 2QB

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Accessories

## Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC 40D TOBU 1PG21G        | Version  |
| Order No.  | <a href="#">1656630000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 21      |
| GTIN (EAN) | 4008190409647              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 40D TOBU 1M32G         | Version  |
| Order No.  | <a href="#">1787060000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 32       |
| GTIN (EAN) | 4032248204304              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 40D TOBU 2M25          | Version  |
| Order No.  | <a href="#">1208380000</a> | HDC enclosures, Size: 6, Protection degree: IP65, IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 25 |
| GTIN (EAN) | 4032248100248              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 40D TOBU 1PG29G        | Version  |
| Order No.  | <a href="#">1656650000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 29      |
| GTIN (EAN) | 4008190409661              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 40D TOBU 1M25G         | Version  |
| Order No.  | <a href="#">1787070000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 25       |
| GTIN (EAN) | 4032248204410              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 16B TOBU 1PG21G        | Version  |
| Order No.  | <a href="#">1656590000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 21  |
| GTIN (EAN) | 4008190409609              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 16B TOBU 1M25G         | Version  |
| Order No.  | <a href="#">1788210000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25   |
| GTIN (EAN) | 4032248205745              |  |
| Qty.       | 1 pc(s).                   |  |

## HDC 16B DODQ 2QB

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC 40D TSBU 1PG29G        | Version  |
| Order No.  | <a href="#">1656540000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 29     |
| GTIN (EAN) | 4008190409555              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 16B TSBU 1PG21G        | Version  |
| Order No.  | <a href="#">1656480000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 21 |
| GTIN (EAN) | 4008190409494              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 40D TSBU 1M25G         | Version  |
| Order No.  | <a href="#">1787010000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 25      |
| GTIN (EAN) | 4032248204250              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 40D TSBU 1PG21G        | Version  |
| Order No.  | <a href="#">1656520000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 21     |
| GTIN (EAN) | 4008190409531              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 16B TSBU 1M40G         | Version  |
| Order No.  | <a href="#">1809620000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 40  |
| GTIN (EAN) | 4032248284979              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 40D TSBU 1M32G         | Version  |
| Order No.  | <a href="#">1787000000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 32      |
| GTIN (EAN) | 4032248204243              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 40D TSBU 1M40G         | Version  |
| Order No.  | <a href="#">1904800000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 40      |
| GTIN (EAN) | 4032248521852              |  |
| Qty.       | 1 pc(s).                   |  |
| Type       | HDC 16B TSBU 1M25G         | Version  |
| Order No.  | <a href="#">1788180000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25  |
| GTIN (EAN) | 4032248205714              |  |
| Qty.       | 1 pc(s).                   |  |

**HDC 16B DODQ 2QB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Cover**



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | HDC 16B DODQ 4B0           | Version  |
| Order No.  | <a href="#">1665260000</a> | HDC enclosures, Size: 6, Protection degree: IP65 (in plugged condition), Cover for lower part of housing, Side-locking clamp on lower side, Standard |
| GTIN (EAN) | 4008190421960              |  |
| Qty.       | 1 pc(s).                   |  |