

SAI-T-5S-PARA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Y connector, M12
Order No.	1009370000
Type	SAI-T-5S-PARA
GTIN (EAN)	4032248713622
Qty.	1 pc(s).

SAI-T-5S-PARA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	29 g
------------	------

Connection data

Group outlet - plug-in connector	M12 socket	Single outlet 1 - plug-in connector	M12 socket
Single outlet 2 - plug-in connector	M12 pin	Tightening torque	M12: 0.8 - 1.2 Nm

Technical data customisable plug-in connectors

Cable glands	M 12	Coding	A-coded
Contact material	CuSn	Contact surface	Gold-plated
Number of poles	5	Pollution severity	3
Protection degree	IP67	Rated current	4 A
Rated voltage	60 V	Temperature range of housing	-25...+85 °C

Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

General data

Cable glands	M 12	Coding	A-coded
Conductor O.D.	-	Connection thread	M12
Contact material	CuSn	Contact surface	Gold-plated
Number of poles	5	Pollution severity	3
Protection degree	IP67	Rated current	4 A
Rated voltage	60 V	Temperature range of housing	-25...+85 °C

Classifications

ETIM 6.0	EC002925	ETIM 7.0	EC002925
ETIM 8.0	EC002925	ETIM 9.0	EC002925
ECLASS 9.0	27-44-01-06	ECLASS 9.1	27-44-01-06
ECLASS 10.0	27-44-01-06	ECLASS 11.0	27-44-01-06
ECLASS 12.0	27-44-01-06	ECLASS 13.0	27-44-01-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	4060c755-8d0b-4d43-bdb3-4ffabe9d7497

Approvals

Approvals



ROHS	Conform
------	---------

SAI-T-5S-PARA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAI-T-5S-PARA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Wiring diagram

