

**WQV 2.5/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 3, Pitch in mm (P): 5.10, Insulated: Yes, 32 A, yellow
Order No.	<a href="#">1053760000</a>
Type	WQV 2.5/3
GTIN (EAN)	4008190058999
Qty.	50 pc(s).

## WQV 2.5/3

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	18 mm	Depth (inches)	0.709 inch
Height	14.2 mm	Height (inches)	0.559 inch
Width	7 mm	Width (inches)	0.276 inch
Net weight	2.26 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

## Material data

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-0		

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

## Cross-connector

Number of cross-connected terminals	3	Rated current, 2-pole	32 A
Rated current, multi-pole	32 A	Tightening torque range for fixing screw	0.4...0.8 Nm
Type	Cross-connector		

## Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

## General

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

## Rating data

Rated current	32 A
---------------	------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

## Approvals

ROHS	Conform
------	---------

## WQV 2.5/3

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Technical data

## Downloads

Approval/Certificate/Document of Con- formity	<a href="#">Confirmation of Standards EN 45545-2_2020-10</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**WQV 2.5/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Cutting and notching tools for cross-connections**

- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

**General ordering data**

Type	WAW 1 NEUTRAL	Version
Order No.	<a href="#">9004500000</a>	Miscellaneous tools
GTIN (EAN)	4008190053925	
Qty.	1 pc(s).	