

IE-BP-V14P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

For protecting your devices against dust and dirt.

General ordering data

Version	Flange-mounted housing, protective cap
Order No.	1058310000
Type	IE-BP-V14P
GTIN (EAN)	4032248799404
Qty.	10 pc(s).

IE-BP-V14P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	22.9 mm	Depth (inches)	0.902 inch
Net weight	4.778 g		

Temperatures

Operating temperature	-40 °C...70
-----------------------	-------------

General data

Colour	black	Housing main material	PA UL 94 V0
Protection degree	IP67	Type of mounting	Indoors only
UL 94 flammability rating	V-0		

Classifications

ETIM 6.0	EC002314	ETIM 7.0	EC002314
ETIM 8.0	EC002314	ETIM 9.0	EC002314
ECLASS 9.0	27-44-02-08	ECLASS 9.1	27-44-02-08
ECLASS 10.0	27-44-02-08	ECLASS 11.0	27-44-02-08
ECLASS 12.0	27-44-02-08	ECLASS 13.0	27-44-02-08

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	Zuken E3.S
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN