

CB-R 350/7,5 NC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Similar to illustration

Releasable and reusable cable ties, suitable for temporary bundling and when open-close function is necessary.

General ordering data

Version	Cable ties, 7.5 x 350 mm, Polyamide 66, 220 N
Order No.	1059240000
Type	CB-R 350/7,5 NC
GTIN (EAN)	4032248806188
Qty.	100 pc(s).

CB-R 350/7,5 NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	2 mm	Depth (inches)	0.079 inch
Height	350 mm	Height (inches)	13.78 inch
Width	7.5 mm	Width (inches)	0.295 inch
Net weight	3.79 g		

Temperatures

Operating temperature range	-40...85 °C
-----------------------------	-------------

Installation materials

Cable diameter, max.	100 mm	For re-opening	Yes
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	220 N	Tensile strength (Pound-force)	49 lbf
UL 94 flammability rating	V-2	UV-resistant	No

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[DE PI830000 160627 001](#)

Catalogues

[Catalogues in PDF-format](#)

CB-R 350/7,5 NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Drawing

