

THM GEW 15/6 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers.

Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

General ordering data

| | |
|--------------------|-------------------------------------------------------|
| Version | THM, Device markers, 6 x 15 mm, white |
| Order No. | 1059780000 |
| Type | THM GEW 15/6 WS |
| GTIN (EAN) | 4032248808175 |
| Qty. | 1 pc(s). |
| compatible printer | 2599430000 2599440000 |

THM GEW 15/6 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 0.3 mm | Depth (inches) | 0.012 inch |
| Height | 6 mm | Height (inches) | 0.236 inch |
| Width | 15 mm | Width (inches) | 0.591 inch |
| Net weight | 384 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -29...80 °C |
|-----------------------------|-------------|

General data

| | | |
|----------------------------------------------|-------------------------------|------------|
| Adhesive | Natural rubber adhesive | |
| Approval acc. to UL 969 | No | |
| Colour | white | |
| Halogen | No | |
| Material | Cotton fabric | |
| Material colour according to resistance code | 9 | |
| Number of markers per combination | 1 Label reel = Device markers | |
| Number of markers per packaging unit | Form of supply | Label reel |
| Number per roll | 10,000 | |
| Number per sheet | 10,000 | |
| Operating temperature range | -29...80 °C | |
| Operating temperature range, max. | 80 °C | |
| Operating temperature range, min. | -29 °C | |
| Printing method | Thermal transfer | |
| UL 94 flammability rating | V-0 | |
| Version | Self-adhesive | |
| Width | 15 mm | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|------------------------------------------|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |

THM GEW 15/6 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM GEW 15/6 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | |
|------------|----------------------------|------------|
| Type | RIBBON MM 110/360 SW | Version |
| Order No. | 2005070000 | Ink ribbon |
| GTIN (EAN) | 4050118390049 | |
| Qty. | 1 pc(s). | |

THM GEW 15/6 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

