

WZAF 70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The additional connection enables a separate voltage tap. This can be used, for example, for the emergency power supply before the main switch or simply as an additional connection within the application.

General ordering data

| | |
|------------|---------------------------------|
| Version | Auxiliary connection (terminal) |
| Order No. | 1066200000 |
| Type | WZAF 70 |
| GTIN (EAN) | 4008190169831 |
| Qty. | 10 pc(s). |

WZAF 70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|-------|-----------------|------------|
| Depth | 10 mm | Depth (inches) | 0.394 inch |
| Height | 30 mm | Height (inches) | 1.181 inch |
| Width | 27 mm | Width (inches) | 1.063 inch |
| Net weight | 8.3 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|---------------|--------|-------------|
| Material | tinned copper | Colour | Silver grey |
|----------|---------------|--------|-------------|

System specifications

| | |
|---------|-----------------------|
| Version | Additional connection |
|---------|-----------------------|

Additional technical data

| | | | |
|--------------------------|---------|---------------------|-----------------------------------------|
| Explosion-tested version | No | Installation advice | Feed-through (bushing), Direct mounting |
| Type of fixing | Plugged | | |

Dimensions

| | |
|-----------------|-------|
| Pitch in mm (P) | 27 mm |
|-----------------|-------|

General

| | |
|---------------------|-----------------------------------------|
| Installation advice | Feed-through (bushing), Direct mounting |
|---------------------|-----------------------------------------|

Rating data

| | |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ECLASS 9.0 | 27-14-11-92 | ECLASS 9.1 | 27-14-11-92 |
| ECLASS 10.0 | 27-14-11-92 | ECLASS 11.0 | 27-14-11-92 |
| ECLASS 12.0 | 27-14-11-92 | ECLASS 13.0 | 27-25-03-08 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|------------------------------------------|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |